

Sub-base VMPA1-IC-AP-S-1

Part number: 533395

FESTO



Data sheet

| Feature | Value |
|--|---|
| Width | 20.2 mm |
| Length | 107.3 mm |
| Width dimension | 10.5 mm |
| Operating pressure | -0.09 MPa...1 MPa -0.9 bar...10 bar |
| Pilot pressure MPa | 0.3 MPa...0.8 MPa |
| Pilot pressure | 3 bar...8 bar |
| Certification | c UL us - Recognized (OL) |
| KC characters | KC EMC |
| CE marking (see declaration of conformity) | As per EU EMC directive As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK instructions for EMC To UK RoHS instructions |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -5 °C...50 °C |
| Product weight | 92 g |
| Electrical connection | M8 Plug |
| Sub-base mounting type | With through-hole |
| Pilot air port 12/14 | M5 |
| Pilot exhaust air port 82/84 | M5 |
| Pneumatic connection 1 | M7 |
| Pneumatic connection 2 | M7 |
| Pneumatic connection 3 | M7 |
| Pneumatic connection 4 | M7 |
| Pneumatic connection 5 | M7 |
| Note on materials | RoHS-compliant |
| Material of sub-base | Die-cast aluminum |