

# Plastic tubing

## PUN-E-6x0,8-BL-500

Part number: 534173

FESTO

Suitable for use with QS push-in connectors, highly flexible, hydrolysis resistant, micron stable, approved for use in food processing.

Type to be discontinued. Available until 2012.



### Data sheet

Feature	Value
Outside diameter	6 mm
Bending radius relevant for flow rate	45 mm
Inside diameter	4.4 mm
Min. bending radius	15 mm
Temperature dependent working pressure	-0.95 ... 8 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-:]
Food-industry approval	FDA 2002/72/EG
Ambient temperature	-35 ... 50 °C
Product weight according to length	0.018 kg/m
Color	blue
Shore hardness	D 52 +/-3
Materials note	Free of copper and PTFE Conforms to RoHS
Materials information for tubing	TPE-U(PU)