

Pneumatic muffler UC-M5-50

Part number: 534217

FESTO



Data sheet

Feature	Value
Mounting position	Any
Pack size	50
Operating pressure	0 MPa...1 MPa 0 bar...10 bar
Flow rate with respect to atmosphere	350 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
Information on operating and pilot media	Operation with oil lubrication possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Noise level	60 dB(A)
Ambient temperature	-10 °C...70 °C
Product weight	0.4 g
Pneumatic connection	M5
Cushioning insert material	PE
Material of screwed plug	PE
Note on materials	RoHS-compliant