


Plug FBS-RJ45-8-GS

Part number: 534494

FESTO



Data sheet

Feature	Value
Width	33 mm
Height	41 mm
Length	20 mm
Product weight	15 g
Ethernet cable specification	Typ: CAT.5 Individual wire diameter: 0.89 - 0.99 mm AWG 24-26, fine wire
Protection against direct and indirect contact	PELV
Approved cable diameter	4 mm...5.4 mm
Degree of protection	IP65 IP67 as per IEC 60529
Ambient temperature	-5 °C...60 °C
Storage temperature	-20 °C...70 °C
Relative air humidity	0 - 90 % Non-condensing
LABS (PWIS) conformity	VDMA24364-B2-L
Housing material	PA-reinforced
Material of screws	Steel
Seals material	NBR