

# Fine filter MS12N-LFM

Part number: 535045

FESTO



## Data sheet

Feature	Value
Series	MS
Size	12
Structural design	Fiber filter
Operating pressure	0.8 bar...20 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [6:8:4] Inert gas
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Storage temperature	-10 °C...60 °C
Type of mounting	Optionally: Line installation With accessories
Mounting position	Vertical +/- 5°
Housing material	Die-cast aluminum
Compressed air filter material	Borosilicate fiber
Material of bowl	Wrought aluminum alloy
Note on materials	RoHS-compliant