

Clevis flange SNCL-12

Part number: 537790

FESTO



Data sheet

Feature	Value
Size	12
Based on norm	ISO 21287
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C...90 °C
Product weight	20 g
Note on materials	RoHS-compliant
Mounting material	Wrought aluminum alloy
Material of bearing	Polymer
Material of screws	Steel Galvanized