

Electronics module VMPA2-FB-EMG-4

Part number: 537984

FESTO



Data sheet

Feature	Value
Diagnostics	Undervoltage of pneumatic valves
Max. no. of valve positions	2
Max. no. of solenoid coils	4
Intrinsic current consumption at load voltage	23 mA
Intrinsic current consumption at operating voltage	8 mA
Nominal pick-up current per solenoid coil	99 mA to 24 ms
Nominal current with current reduction	18 mA after 24 ms
Corrosion resistance class (CRC)	1 - Low corrosion stress (when installed)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	20 g
Housing material	POM
Note on materials	RoHS-compliant