

Support profile HMIA-E07- -

Part number: 539379

FESTO



Data sheet

Feature	Value
Max. profile length	3000 mm
Mounting position	Any
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Product weight by length	2.34 kg/m
Adapter material	Wrought aluminum alloy Anodized