


Connecting cable

NEBU-M5G4-K-5-Q3-LE3

Part number: 539508

FESTO

for proximity sensors, position transmitter, pressure switch, flow sensors, visual and inductive sensors.



Data sheet

Feature	Value
Cable attribute	Suitable for chain link trunking
Operating voltage range AC	30 V
Operating voltage range DC	30 V
Permissible current load	1.7 A
Degree of contamination	3
Protection class	IP65 IP67
Max. tightening torque, plug socket	0.3 Nm
Min. cable bending radius	30 mm
Wire ends	Wire end ferrule
Electrical connection	Straight socket / cable M5x0.5 / open end 4-pole / 3-wire
Cable structure	3x0,14
Cable diameter	2.9 mm
Cable length	5 m
Cable type	LiFY11Y
Nominal conductor cross-section	0.14 mm ²
Mounting type	With knurled nut With sleeve nut
Color, wires	blue brown Black
Housing color	Black
Cable sheath color	Grey
Materials information for locknut	Brass Nickel plated
Materials information, housing	TPE-U(PU)
Materials information, cable sheaths	TPE-U(PU)
Material information for crimp connectors	Brass Gold plated