

# Heavy-duty tubing PAN-R-10X1,9-SI

Part number: 541677

FESTO



## Data sheet

Feature	Value
Outside diameter	10 mm
Bending radius relevant for flow rate	44 mm
Inside diameter	6.2 mm
Min. bending radius	25 mm
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0.095 MPa...3.5 MPa -0.95 bar...35 bar -13.775 psi...507.5 psi
Certification	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-30 °C...80 °C
Product weight by length	0.0498 kg/m
Pneumatic connection	For plug connection outside diameter 10 mm
Color	Silver
Shore hardness	D 62 +/-3
Note on materials	RoHS-compliant
Material of pneumatic tubing	TPE-A