

# Ball valve

## VZBA-R38-63-32L-F0304-R

Part number: 542007

FESTO

In stainless steel version, 3-way ball valve with internal thread, L hole  
90 degrees with ISO 5211 interface for mounting on semi-rotary  
actuators DRD, DRE and DAPS.



### Data sheet

Feature	Value
Design structure	3-way ball valve L hole
Type of actuation	mechanical
Sealing principle	soft
Mounting type	Line installation
Process valve connection	Rp3/8
Switching position indicator	Slot direction = flow direction
Flange hole pattern	F03 F04
Inside diameter	12.5 mm
Nominal diameter DN	10
Manual override	None
Flow direction	reversible
Nominal pressure of process valve	63
Actuation torque	8 Nm
Operating medium	Inert gases Neutral fluids
Medium temperature	-10 ... 140 °C
Flow rate Kv, L hole	4.5 m <sup>3</sup> /h
Flow rate tolerance Kv	+/- 20 %
Materials note	Contains PWIS substances
Materials information, housing	High alloy steel, non-corrosive
Material number for housing	1.4408
Materials information for seals	PTFE
Material information, globe	High alloy steel, non-corrosive
Material number for ball	1.4401
Materials information for shaft	High alloy steel, non-corrosive
Material number for shaft	1.4401
Product weight	700 g
CE symbol (see declaration of conformity)	according to EU printing device guideline
Corrosion resistance classification CRC	3