


Linear gantry DHSL-DGC25-SLT16

Part number: 542984

FESTO

comprising rodless actuator unit and compact mini slide, dynamic and precise. Defined interfaces to Festo's rotary and gripper range. Order as a mounting kit or completely assembled and installed.

Please click above on symbol FAX request, to obtain a non-binding offer to fulfill your requirements.



Data sheet

Feature	Value
Assembly	Linear gantry 1.0
Effective load	0 ... 2 kg
Drive unit, Z axis	SLT-16
Drive system, Z axis	Pneumatic
Stroke, Z axis	0 ... 150 mm
Repetition accuracy in the end position, Z axis	± 0,02 mm
Drive unit, Y axis	DGC-25
Drive system, Y axis	Pneumatic
Stroke, Y axis	0 ... 3,000 mm
Repetition accuracy in the end position, Y axis	± 0,02 mm