

Three-dimensional gantry


DHSR-DGE25RF-2DGE25RF-HMPL20

Part number: 543036

FESTO

comprising electric toothed belt axis with roller guides, vertical modular handling axis, precise positioning. Defined interfaces to Festo's rotary and gripper range. Order as a mounting kit or completely assembled and installed.

Please click above on symbol FAX request, to obtain a non-binding offer to fulfill your requirements.



Data sheet

Feature	Value
Assembly	three-dimensional gantry 2.0
Effective load	0 ... 4 kg
Drive unit, Z axis	HMPL-20
Drive system, Z axis	Pneumatic
Intermediate position, Z axis	x1
Stroke, Z axis	0 ... 200 mm
Repetition accuracy in the end position, Z axis	± 0,02 mm
Repetition accuracy in the intermediate position, Z axis	± 0,02 mm
Drive unit, Y axis	2x DGE-25-ZR-RF
Drive system, Y axis	Electrical Toothed belt with roller guide 2x
Intermediate position, Y axis	Any
Stroke, Y axis	0 ... 1,000 mm
Repetition accuracy in the end position, Y axis	± 0,1 mm
Repetition accuracy in the intermediate position, Y axis	± 0,1 mm
Drive unit, X axis	DGE-25-ZR-RF
Drive system, X axis	Electrical Toothed belt with roller guide
Intermediate position, X axis	Any
Stroke, X axis	0 ... 3,000 mm
Repetition accuracy in the end position, X axis	± 0,1 mm
Repetition accuracy in the intermediate position, X axis	± 0,1 mm