

# Connecting component KVI-CP-3-SSD

Part number: 543252

FESTO



## Data sheet

Feature	Value
Type of mounting	With external thread
Product weight	48 g
Electrical connection	5-pin Socket Straight socket/straight plug M9 Plug
DC operating voltage range	60 V
Degree of protection	IP65 IP67
Ambient temperature	-20 °C...80 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Housing material	Brass Nickel-plated
Seals material	NBR
Mounting position	Any