

Connection block CPE18-PRS-3/8-9

Part number: 543846

FESTO



Data sheet

| Feature | Value |
|---|--|
| Width dimension | 26 mm |
| Mounting position | Any |
| Max. no. of valve positions | 9 |
| Max. no. of pressure zones | 2 |
| Burst pressure | 5 MPa 50 bar 725 psi |
| Operating pressure | -0.09 MPa...1 MPa -0.9 bar...10 bar |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Temperature of medium | -5 °C...50 °C |
| Ambient temperature | -5 °C...50 °C |
| Max. tightening torque for valve mounting | 2 Nm |
| Product weight | 1257 g |
| Manifold block type of mounting | With through-hole |
| Pneumatic valve mounting type | With internal thread |
| Pneumatic connection 1 | G3/8 |
| Pneumatic connection 3 | G3/8 |
| Pneumatic connection 5 | G3/8 |
| Note on materials | RoHS-compliant |
| Manifold rail material | Wrought aluminum alloy |