



Vertical pressure supply plate

VABF-S3-2-P1A3-G18

Part number: 544435

FESTO

For valve manifold VDMA-01/02, standard port pattern to 15407-1, for mounting between manifold sub-base and valve.



Data sheet

Feature	Value
Width	18 mm
Based on the standard	ISO 15407-1
Assembly position	Any
Pneumatic vertical stacking	Alternative pressure supply for 1
Working pressure	-0.9 ... 10 bar
Standard nominal flow rate	500 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Protection class	IP65 NEMA 4
Ambient temperature	-5 ... 50 °C
Product weight	146 g
Vertical stacking type of mounting	on manifold block on individual subbase
Materials note	Conforms to RoHS
Material housing	Aluminum die cast