


# Coupling plug KS-PK-6

Part number: 546078  
Product to be discontinued

FESTO

Type to be discontinued. Available until 2023. See Support Portal for alternative products.



## Data sheet

Feature	Value
Nominal size	5.3 mm
Working pressure	-0.95 ... 12 bar
Standard nominal flow rate	670 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 60 °C
Product weight	32 g
Pneumatic connection	PK-6