

# Quick coupling EAMC-40-66-11-15

Part number: 550998

FESTO



## Data sheet

Feature	Value
Diameter of holder 1	11 mm
Diameter of holder 2	15 mm
Size	40
Nominal length	66 mm
Mounting position	Any
Max. rotational speed	6500 1/min
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	42.3 kgmm <sup>2</sup>
Transferable torque	21 Nm
Product weight	139 g
Note on materials	RoHS-compliant