

Operator unit CDSA-D1-VX

Part number: 552103
Product to be discontinued

FESTO

for multi-axis controller CMXR-C1

Type to be discontinued. Available until 2017. See Support Portal for alternative products.



Data sheet

Feature	Value
Max connector cable length	20 m
User memory	256 Mbyte
Number of function keys	31
Number of colors	64 k
Number of system LEDs	4
Display	TFT color
Display property	Touchscreen
Display size	6,5"
Control elements	2 accept buttons Emergency stop
Backup battery	Yes
Operating voltage range DC	19 ... 30 V
Display resolution	VGA, 640x480 Pixel
Current consumption at nominal operating voltage	0,4 A
CE symbol (see declaration of conformity)	according to EU-EMV guideline
Storage temperature	-20 ... 70 °C
Relative air humidity	5 - 95 % non-condensing
Protection class	IP65
Ambient temperature	0 ... 50 °C
Product weight	1,250 g
USB interface	Yes
Ethernet interface	RJ45 10/100 MBd 2nd Ethernet interface, optical 10 MBd
Materials note	Contains PWIS substances Conforms to RoHS
Materials information, housing	ABS
Area of application	Only with CMXR-C1