

Cable

NESC-C-D1-10-C1

Part number: 552105
Product to be discontinued

[for operator unit CDSA](#)

Type to be discontinued. Available until 2017. See Support Portal for alternative products.

FESTO



Data sheet

Feature	Value
Cable attribute	For static applications
Corrosion resistance classification CRC	0
Protection class	IP65
Ambient temperature with flexible cable installation	-40 ... 70 °C
Ambient temperature	-40 ... 70 °C
Cable length	10 m
Cable interface	Coninvers plug, 17-pin RJ45 Socket strip 11-pin
Mounting type	With cable sleeve at one end
Cable sheath color	Red
Materials note	Conforms to RoHS
Materials information, cable sheaths	TPE-U(PUR)