

Bellows kit DADB-V6-32-S51-125

Part number: 553273

FESTO



Data sheet

Feature	Value
Outside diameter	38 mm
Size	32
Stroke range	51 mm...125 mm
Piston rod extension	47 mm
Design	Round
Mounting position	Any
Structural design	Bellows kit with ducted exhaust air
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Media resistance	Stäube Chips Oils Grease Petrol
Degree of protection	IP54
Ambient temperature	-10 °C...80 °C
Product weight	41 g
Type of mounting	Push-on With threaded pin
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Adaption parts material	PA-reinforced
Seals material	NBR
Bellows material	NBR
Threaded pin material	High-alloy stainless steel