

# Bellows kit DADB-V6-40-S476-500

Part number: 553309

FESTO



## Data sheet

| Feature                          | Value                                       |
|----------------------------------|---|
| Outside diameter                 | 46 mm                                       |
| Size                             | 40  |
| Stroke range                     | 476 mm...500 mm                             |
| Piston rod extension             | 131 mm                                      |
| Design                           | Round                                       |
| Mounting position                | Any   |
| Structural design                | Bellows kit<br>with ducted exhaust air      |
| Corrosion resistance class (CRC) | 3 - High corrosion stress                   |
| LABS (PWIS) conformity           | VDMA24364-B2-L                              |
| Media resistance                 | Stäube<br>Chips<br>Oils<br>Grease<br>Petrol |
| Degree of protection             | IP54  |
| Ambient temperature              | -10 °C...80 °C                              |
| Product weight                   | 144 g                                       |
| Type of mounting                 | Push-on<br>With threaded pin                |
| Pneumatic connection             | G1/8  |
| Note on materials                | RoHS-compliant                              |
| Adaption parts material          | PA-reinforced                               |
| Seals material                   | NBR   |
| Bellows material                 | NBR   |
| Threaded pin material            | High-alloy stainless steel                  |