


Input module CECX-E-4E-T-P1

Part number: 553973

FESTO



Data sheet

Feature	Value
Corrosion resistance classification CRC	0 - No corrosion stress
Authorization	c UL us - Listed (OL)
Materials note	Contains PWIS substances Conforms to RoHS
Power consumption 24 V	2.5 W
Power consumption 5 V	0.3 W
Ambient temperature	5 ... 55 °C
Storage temperature	-40 ... 70 °C
Relative air humidity	10 - 95 %
Protection class	IP20
Safety class	III
Product weight	134 g
Test for insensitivity to vibration	EN 60068-2-6 FC 5 - 9 Hz 3,5 mm 9 - 150 Hz 1g
Test for insensitivity to shock	EN 60068-2-27 EA 15 g, 11 ms (half sine)
Electrical connector technology, I/O	Socket strip, grid 5.08 mm
Analog inputs, number	4
Analog inputs, resolution	14 bit
Analog inputs, signal range	PT 100 (-100 °C to 850 °C)
Analog inputs, value of least significant bit (LSB)	0,058 °C
Analog inputs, absolute precision at 25 °C	± 0,01%
Analog inputs, galvanic isolation	No
Analog inputs, input resistance	10 MOhm
Internal cycle time	2 ms