


# Axial kit EAMM-A-L48-87A

Part number: 560683

FESTO



## Data sheet

Feature	Value
Nominal length	44 mm
Mounting position	Any
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Transferable torque	12.5 Nm
Product weight	590 g
Interface code, actuator	L48
Interface code, motor in	87A
Note on materials	RoHS-compliant