

Plastic tubing PUN-V0-12X2-SW-C

Part number: 561701

FESTO



Data sheet

Feature	Value
Outside diameter	12 mm
Bending radius relevant for flow rate	55 mm
Inside diameter	8 mm
Min. bending radius	19 mm
Tubing characteristics	Suitable for energy chains
Operating pressure for entire temperature range	-0.095 MPa...0.7 MPa -0.95 bar...7 bar -13.775 psi...101.5 psi
Temperature-dependent operating pressure	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Information on operating pressure	Water: max. 0.6 MPa at max. 50 °C
Certification	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free)
Material fire test	UL94 V-0 (3mm) UL94 V-2 (0.75mm)
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-35 °C...60 °C
Note on ambient temperature	unpressurised use up to 90°C
Product weight by length	0.08 kg/m
Pneumatic connection	For plug connection outside diameter 12 mm
Color	Black
Information on color	Deviates from the standard color due to flame protection
Shore hardness	D 54 +/-3
Note on materials	RoHS-compliant
Material of pneumatic tubing	TPE-U(PU)