

Push-in L-fitting QBLF-1/2-3/8-U

Part number: 564666

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal width	0,276 in
Type of seal on screwed plug	Coating
Mounting position	Any
Design	L-shape
Pack size	5
Structural design	Push-pull principle
Operating pressure for entire temperature range	0.095 MPa...1 MPa 0.95 bar...10 bar 13.775 psi...145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	0 °C...60 °C
Max. tightening torque	20,7 ft-lbf
Product weight	1157 oz
Type of mounting	External hexagon 5/16
Pneumatic connection 1	internal thread 1/2 NPT
Pneumatic connection 2	for pneumatic tubing outside diameter 3/8" "
Ambient temperature Fahrenheit	32 °F...140 °F
Releasing ring color	Gray
Note on materials	RoHS-compliant
Housing material	Brass, nickel-plated PBT
Material of threaded seal	PTFE
Releasing ring material	POM
Material of tubing seal	NBR
Material of tube retaining claw	High-alloy stainless steel