

Water trap MS6-LWS-3/8-U-V

Part number: 564869

FESTO



Data sheet

Feature	Value
Size	6
Series	MS
Mounting position	Vertical +/- 5°
Condensate drain	Fully automatic
Structural design	Centrifugal separator
Max. condensate volume	38 ml
Bowl guard	Integrated as metal bowl guard
Degree of condensate separation	99 %
Operating pressure	2 bar...12 bar
Standard nominal flow rate	3500 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:~] Inert gas
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
For use in the food industry	See supplementary material information
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [7:7:4]
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	820 g
Type of mounting	Optionally: Line installation With accessories
Pneumatic connection 1	G3/8
Pneumatic connection 2	G3/8
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	Die-cast aluminum
Material of bowl	Wrought aluminum alloy
Inspection window material	PA