

# Plastic tubing PEN-U

Part number: 567448

FESTO



## Data sheet

Feature	Value
External-Ø inches	5/8
Tubing characteristics	Suitable for energy chains in applications with higher cycle rates
Pneumatic tubing test conditions	Suitability for energy chains: > 5 million cycles according to FN 942021
Temperature-dependent operating pressure	-14,4 psi...58 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration at <a href="http://www.festo.com">www.festo.com</a>
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-22 °F...140 °F
Pneumatic connection	For plug connection outside diameter 5/8" "
Color	Blue Brown Yellow Green Natural Red Black Silver White
Note on materials	RoHS-compliant
Material of pneumatic tubing	PE