


Plastic tubing PUN-H-3/8-BL-500-HA

Part number: 568016

FESTO



Data sheet

Feature	Value
External-Ø inches	3/8
Bending radius relevant for flow rate	0,171 Feet
Min. bending radius	0,081 Feet
Application note	TPE-U Ether based
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-14,4 psi...145 psi
Information on operating pressure	Water: temperature-dependent operating pressure, see diagram, max. 0.3 MPa at 0 - 60 °C
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free)
Material fire test	UL94 HB
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Statically installed element, no meaningful evaluation possible according to ISO 14644-1
For use in the food industry	See supplementary material information
Ambient temperature	-31 °F...145 °F
Product weight by length	oz/ft
Pneumatic connection	For plug connection outside diameter 3/8" "
Color	Blue
Shore hardness	D 52 +/-3
Note on materials	RoHS-compliant
Material of pneumatic tubing	TPE-U(PU)