

Plastic tubing PEN-3/16-SW-150-CB

Part number: 569882

FESTO



Data sheet

Feature	Value
External-Ø inches	3/16
Bending radius relevant for flow rate	0,075 Feet
Min. bending radius	0,039 Feet
Tubing characteristics	Suitable for energy chains in applications with higher cycle rates
Pneumatic tubing test conditions	Suitability for energy chains: > 5 million cycles according to FN 942021
Temperature-dependent operating pressure	-14,4 psi...145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-] Water as per manufacturer's declaration at www.festo.com
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-22 °F...140 °F
Product weight by length	oz/ft
Pneumatic connection	For plug connection outside diameter 3/16" "
Color	Black
Shore hardness	D 52 +/-3
Note on materials	RoHS-compliant
Material of pneumatic tubing	PE