

Plastic tubing PLN-1/4-NT-150-CB

Part number: 569899

FESTO



Data sheet

Feature	Value
External-Ø inches	1/4
Bending radius relevant for flow rate	0,105 Feet
Min. bending radius	0,039 Feet
Temperature-dependent operating pressure	-14,4 psi...203 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com
LABS (PWIS) conformity	VDMA24364-B1/B2-L
For use in the food industry	See supplementary material information
Ambient temperature	-22 °F...176 °F
Product weight by length	oz/ft
Pneumatic connection	For plug connection outside diameter 1/4" "
Color	Natural
Shore hardness	D 52 +/-3
Note on materials	RoHS-compliant
Material of pneumatic tubing	PE