

Bellows kit

EADB-V1-32-S201-300

Part number: 570264

FESTO



Data sheet

| Feature | Value |
|---|--|
| Outside diameter | 46 mm |
| Size | 32 |
| Stroke range | 201 ... 300 mm |
| Piston rod extension | 88 mm |
| Design | Round |
| Assembly position | Any |
| Design structure | Bellows kit with ducted exhaust air |
| Corrosion resistance classification CRC | 3 |
| Resistance to media | Dust Chippings Oils Grease Gasolines |
| Protection class | IP65 to IEC 60529 |
| Ambient temperature | -10 ... 80 °C |
| Moving mass | 80 g |
| Product weight | 122 g |
| Mounting type | slip-on With threaded pin |
| Pneumatic connection | G1/8 |
| Materials note | Conforms to RoHS |
| Note on materials: Adapter components | Wrought Aluminum alloy Anodized |
| Materials information for seals | NBR |
| Note on materials: Bellows | NBR |
| Threaded stud material information | High alloy steel, non-corrosive |