

Plastic tubing PAN-14X2-SI

Part number: 570392

FESTO



Data sheet

Feature	Value
Outside diameter	14 mm
Bending radius relevant for flow rate	80 mm
Inside diameter	10 mm
Min. bending radius	50 mm
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0.095 MPa...1.7 MPa -0.95 bar...17 bar -13.775 psi...246.5 psi
Certification	German Technical Control Board (TÜV)
Maritime classification	See certificate
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-30 °C...80 °C
Product weight by length	0.077 kg/m
Pneumatic connection	For plug connection outside diameter 14 mm
Color	Silver
Shore hardness	D 55 +/-3
Note on materials	RoHS-compliant
Material of pneumatic tubing	TPE-A