

Manifold rail VABM-L1-10G-G18-24-GR

Part number: 573433

FESTO



Data sheet

| Feature | Value |
|----------------------------------|-------------------------------|
| Width dimension | 10.5 mm |
| Mounting position | Any |
| Max. no. of valve positions | 24 |
| Certification | c UL us - Recognized (OL) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -20 °C...60 °C |
| Product weight | 1009 g |
| Pilot air port 12/14 | M5 |
| Pilot exhaust air port 82/84 | M5 |
| Pneumatic connection 1 | G1/8 |
| Pneumatic connection 3 | G1/8 |
| Pneumatic connection 5 | G1/8 |
| Note on materials | RoHS-compliant |
| Manifold rail material | Wrought aluminum alloy |