

# Manifold rail VABM-L1-14G-G14-7-GR

Part number: 573492

FESTO



## Data sheet

| Feature                          | Value                         |
|----------------------------------|-------------------------------|
| Width dimension                  | 16 mm                         |
| Mounting position                | Any                           |
| Max. no. of valve positions      | 7                             |
| Certification                    | c UL us - Recognized (OL)     |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity           | VDMA24364-B1/B2-L             |
| Storage temperature              | -20 °C...60 °C                |
| Product weight                   | 1212 g                        |
| Pilot air port 12/14             | M5                            |
| Pilot exhaust air port 82/84     | M5                            |
| Pneumatic connection 1           | G1/4                          |
| Pneumatic connection 3           | G1/4                          |
| Pneumatic connection 5           | G1/4                          |
| Note on materials                | RoHS-compliant                |
| Manifold rail material           | Wrought aluminum alloy        |