

Clevis foot LBN-12/16

Part number: 6058

FESTO



Data sheet

Feature	Value
Size	12/16
Mounting position	Any
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% copper by mass are excluded from use. Exception are printed circuit boards, cables, electrical connectors and coils
Ambient temperature	-40 °C...150 °C
Product weight	40 g
Note on materials	RoHS-compliant
Mounting material	Steel Galvanized
Bolt material	Steel Galvanized
Fuse material	Spring steel, galvanized