

End cap CV-PK-4-B

Part number: 6214

FESTO

For plastic tubing connectors and barbed fittings.



Data sheet

| Feature | Value |
|--|--|
| Container size | 10 |
| Temperature-dependent operating pressure | -0.095 ... 1 MPa |
| Temperature dependent working pressure | -0.95 ... 10 bar |
| Temperature-dependent operating pressure | -13.775 ... 145 psi |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| PWIS conformity | VDMA24364-B2-L |
| Ambient temperature | -10 ... 80 °C |
| Pneumatic connection, port 1 | For tubing outside diameter 6 mm for barbed connector internal diameter 4 mm with nut |
| Materials note | Conforms to RoHS |
| Material cap | TPE-U(PU) |