

Common supply manifold VABM-B10-25-N12-6-P53

Part number: 8026232

FESTO



Data sheet

Feature	Value
Grid dimension	27.5 mm
Assembly position	Any
Max. number of valve positions	6
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Product weight	586 g
Mounting type	With mounting bracket
Pneumatic connection, port 1	1/2 NPT
Materials note	Conforms to RoHS
Material manifold	Wrought Aluminum alloy