


Connection block VABM-B10-25S-N38-10-P3

Part number: 8026314

FESTO



Data sheet

| Feature | Value |
|----------------------------------|-------------------------------|
| Width dimension | 27.5 mm |
| Mounting position | Any |
| Max. no. of valve positions | 10 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Product weight | 1321 g |
| Type of mounting | With through-hole |
| Pneumatic connection 1 | 3/8 NPT |
| Pneumatic connection 3 | 3/8 NPT |
| Note on materials | RoHS-compliant |
| Manifold rail material | Wrought aluminum alloy |