

# Y-fitting NPFC-Y-3G38-F

Part number: 8030229

FESTO



## Data sheet

| Feature                          | Value  |
|----------------------------------|--|
| Threaded fitting material        | Brass, nickel-plated                         |
| Pack size                        | 10   |
| Operating pressure               | -0.95 bar...50 bar                           |
| Operating medium                 | Compressed air as per ISO 8573-1:2010 [:-:-] |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress                     |
| LABS (PWIS) conformity           | VDMA24364-B1/B2-L                            |
| Ambient temperature              | -20 °C...150 °C                              |
| Product weight                   | 91.9 g                                       |
| Pneumatic connection 1           | G3/8   |
| Pneumatic connection 2           | G3/8   |
| Note on materials                | RoHS-compliant                               |