

# Extension NPFC-E2-2G18-FM

Part number: 8030302

FESTO



## Data sheet

| Feature                          | Value   |
|----------------------------------|---|
| Threaded fitting material        | Brass, nickel-plated                          |
| Pack size                        | 10  |
| Operating pressure               | -0.95 bar...50 bar                            |
| Operating medium                 | Compressed air as per ISO 8573-1:2010 [:-::-] |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress                      |
| LABS (PWIS) conformity           | VDMA24364-B1/B2-L                             |
| Ambient temperature              | -20 °C...150 °C                               |
| Product weight                   | 21.4 g  |
| Pneumatic connection 1           | G1/8  |
| Pneumatic connection 2           | G1/8  |
| Note on materials                | RoHS-compliant                                |