


# Sub-base VMPAL-AP-14-T135-RV

Part number: 8034560

FESTO



## Data sheet

| Feature                                  | Value  |
|--|--|
| Width                                    | 14 mm<br>14.9 mm   |
| Length                                   | 107.3 mm   |
| Width dimension                          | 14.9 mm  |
| Pressure zone separation                 | Channels 1, 3 and 5  |
| Integrated function                      | Non-return valve   |
| Max. no. of valve positions              | 1  |
| Flow direction                           | Non-reversible   |
| Valve manifold design                    | Valve sizes can be mixed   |
| Operating pressure                       | -0.09 MPa...1 MPa<br>-0.9 bar...10 bar                             |
| Pilot pressure MPa                       | 0.3 MPa...0.8 MPa  |
| Pilot pressure                           | 3 bar...8 bar  |
| Suitability for vacuum                   | no   |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 3 - High corrosion stress  |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L  |
| Ambient temperature                      | -5 °C...50 °C  |
| Product weight                           | 35 g   |
| Pneumatic connection 2                   | for 14 mm cartridge  |
| Pneumatic connection 4                   | For 14 mm cartridge  |
| Note on materials                        | RoHS-compliant   |
| Material of sub-base                     | PA-reinforced  |