

# Flanged pressure gauge PAGN-P-40-1M-G14

Part number: 8037006

FESTO



## Data sheet

Feature	Value
Display range	0 MPa...1 MPa
Conforms to standard	EN 837-1
Pressure gauge nominal size	40
Explosion prevention and protection	Observe the information on the certificate Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Structural design	Bourdon tube pressure gauge
Type of mounting	Front panel mounting
Operating medium	Inert gas Neutral liquids
Operating pressure	0 MPa...1 MPa 0 bar...10 bar 0 psi...145 psi
Intermittent load factor	0.66
Measurement accuracy class	2.5
Degree of protection	IP43
Storage temperature	-40 °C...70 °C
Temperature of medium	-20 °C...60 °C
Ambient temperature	-20 °C...60 °C
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS-compliant
Connection position	Centered on rear side
Pneumatic connection	G1/4
Materials in contact with the media	Brass
Material of screwed plug	Brass
Housing material	ABS

<b>Feature</b>	<b>Value</b>
Inspection window material	SAN
Fastening ring material	Steel
Material of screws	Steel
Housing colour	Black
Product weight	80 g
Information on operating and pilot media	No acetylene No oxygen
Scale	Double scale MPa (external) bar (internal)