

Fixed restrictor VFFG-T-F6-10

Part number: 8047355

FESTO

This type is suitable for vacuum.



Data sheet

| Feature | Value |
|------------------------------------|---|
| Valve function | Throttle function |
| Mounting type | Tapped |
| Operating pressure MPa | -0.09 ... 1 MPa |
| Working pressure | -0.9 ... 10 bar |
| Ambient temperature | -5 ... 60 °C |
| Authorization | c UL us - Recognized (OL) |
| Size | For ø 5.8 mm |
| Nominal size | 1.05 mm |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| PWIS conformity | VDMA24364-B1/B2-L |
| Storage temperature | -10 ... 60 °C |
| Product weight | 1.2 g |
| Materials note | Conforms to RoHS |