


Axial kit EAMM-A-N38-70GA

Part number: 8063586

FESTO



Data sheet

Feature	Value
Mounting position	Any
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Transferable torque	12.5 Nm
Product weight	810 g
Interface code, actuator	N38
Interface code, motor in	70GA
Note on materials	RoHS-compliant