

Manifold rail VABM-P7-18M-G18-M5-4

Part number: 8076386

FESTO



Data sheet

| Feature | Value |
|---|-------------------------------|
| Width dimension | 18 mm |
| Structural design | Connection direction at side |
| Max. no. of valve positions | 4 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Max. tightening torque for valve mounting | 0.6 Nm |
| Product weight | 180 g |
| Pneumatic connection 1 | G1/8 |
| Pneumatic connection 2 | M5 |
| Note on materials | RoHS-compliant |
| Manifold rail material | Wrought aluminum alloy |