


# Mains filter CAMF-C6-F-C20-3A

Part number: 8088929

★ Core product range

FESTO



## Data sheet

Feature	Value
Short circuit strength	No
Acceptable current load at 40°C	20 A
Operating voltage range AC	0 ... 250 V
Line frequency	0 ... 400 Hz
Insulation voltage	1,100 V
Authorization	ENEC UL - Recognized (OL) c UL - Recognized (OL)
CE symbol (see declaration of conformity)	in accordance with EU RoHS directive
PWIS conformity	VDMA24364 zone III
Storage temperature	-25 ... 100 °C
Protection class	IP20
Ambient temperature	-25 ... 100 °C
Product weight	700 g
Mounting type	Mounting plate, bolted
Materials note	Conforms to RoHS
Assembly position	Horizontal
Electrical connection 1, function	Power supply
Electrical connection 1, connection type	Terminal strip
Electrical connection 1, connection technology	Screwed terminal
Electrical connection 1, number of pins/wires	2
Electrical connection 1, occupied pins/wires	2
Electrical connection 1, conductor cross section	4 ... 6 mm <sup>2</sup>
Electrical connection 2, function	Power supply
Electrical connection 2, connection type	Terminal strip
Electrical connection 2, connection technology	Screwed terminal
Electrical connection 2, number of pins/wires	2
Electrical connection 2, occupied pins/wires	2
Electrical connection 2, conductor cross section	4 ... 6 mm <sup>2</sup>