


Axial kit EAMM-A-V32-40RA

Part number: 8094180

FESTO



Data sheet

Feature	Value
Nominal length	39 mm
Mounting position	Any
Max. rotational speed	10000 1/min
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	0.19 kgmm ²
Transferable torque	1.5 Nm
Product weight	114 g
Interface code, actuator	V32
Interface code, motor in	40RA
Note on materials	RoHS-compliant