


# Axial kit EAMM-A-T46-85AA

Part number: 8096186

FESTO



## Data sheet

Feature	Value
Nominal length	55 mm
Mounting position	Any
Max. rotational speed	8000 1/min
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	3.2 kgmm <sup>2</sup>
Transferable torque	10 Nm
Product weight	817 g
Interface code, actuator	T46
Interface code, motor in	85AA
Note on materials	RoHS-compliant