


Control plate DADG-FM-F9-VDE2

Part number: 8104802

FESTO



Data sheet

Feature	Value
Based on the standard	VDI/VDE 3845 (NAMUR) VDI/VDE 3847-2
Assembly position	Any
Operating pressure MPa	0.2 ... 0.8 MPa
Working pressure	2 ... 8 bar
Operating pressure	29 ... 116 psi
Nominal operating pressure	0.6 MPa
Nominal working pressure	6 bar
Nominal operating pressure (psi)	87 psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Pressure dew point 10°C below ambient temperature/temperature of medium Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364 zone III
Ambient temperature	-20 ... 80 °C
Product weight	1,340 g
Pneumatic connection	G1/4
Materials note	Conforms to RoHS
Material seals	EPDM NBR
Material threaded pin	High alloy steel, non-corrosive
Material plate	Anodised wrought aluminium alloy
Material screws	High alloy steel, non-corrosive